

Decorator Series Specification
Grade, Rocker Switches, General
Purpose AC, Illuminated Three Way,
20A 120/277V AC, Back and Side
Wired

By Hubbell Wiring Device-Kellems
Catalog # [DS320ILBK](#)



Switches and Lighting Controls, Decorator Series Specification
Grade, Rocker Switches, General Purpose AC, Illuminated Three
Way, 20A 120/277V AC, Back and Side Wired, Black

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Action	SPDT
Catalog Number	DS320ILBK
EU RoHS Indicator	Contact Manufacturer
Indicator	Light On with Load Off
Indicator(s) Type	Blue LED
Item Type	Three Way Style Line Illuminated Decorator Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Illuminated
Specifications	<ul style="list-style-type: none">• Contacts - Silver Alloy• Contacts - Silver Alloy• Ground Screw - Brass (Green)

Style	Three Way
Type	Rocker/Decorator
UPC	783585189208

Dimensions

Dimensions	4.28 in x 1.43 in x 1.54 in
Height	1.54 in
Length	4.28 in
Weight	0.2 lb
Width	1.43 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK D-16 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2444_INSTALLINST](#)
[Sales Drawings - WDK_DS320I_DRAWING_PDF](#)

[Specifications - DS320ILBK Specification Sheet French](#)
[Specifications - Wiring DS320ILBK Specification Sheet](#)
[Specifications - DS320ILBK Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-DS320ILBK-SPEC-EN | REV 4/2025