

Switches and Lighting Controls,
Decorator Rocker Switch, Single
Pole, Momentary Contact, 100mA
30V DC, Single Button, White

By Hubbell Wiring Device-Kellems
Catalog # [DSM30W1](#)



Switches and Lighting Controls, Decorator Rocker Switch, Single Pole, Momentary Contact, 100mA 30V DC, Single Button, White

Features

- Available latching or momentary contact
- Mounts to standard single gang box
- Attractive, architectural design

General

Catalog Number	DSM30W1
Contact Configuration	Momentary
EU RoHS Indicator	No
Humidity	10% to 90% non-condensing relative humidity
Item Type	Low Voltage Switch
Number Of Poles	Single Pole
Operating Temperature	32°F to 122°F (0°C to 50°C)
Series	• Dual • Ultrasonic • Passive Infrared
Style	Switches
Type	Accessories
UPC	783585159386

Dimensions

Length	4.87 in
Width	2.44 in

Electrical Ratings

Voltage Rating	24 VDC
Voltage Rating Description	24V DC

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - WDK E-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2432_INSTALLINST](#)
- [Literature - Load Control Application Guide](#)
- [Literature - Load:Logic® Control Panels](#)
- [Specifications - DSM30W1 Specification Sheet French](#)
- [Specifications - DSM30W1 Specification Sheet](#)
- [Specifications - Wiring DSM30W1 Specification Sheet](#)
- [Warranty - HMOSS Occupancy Motion Sensors](#)