



# Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 3/4", 100 feet

By Hubbell Wiring Device-Kellems  
Catalog # [G1075](#)



Kellems® PolyTuff® I Non-Metallic Liquidtight 3/4" Conduit, 100 feet.

## Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

## Application

UL1660

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"> <li>• Electrical - Voltage Rating - 600V Maximum</li> <li>• Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)</li> <li>• Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)</li> <li>• Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)</li> </ul>
Type	<ul style="list-style-type: none"> <li>• PolyTuff® I Liquidtight Conduit</li> <li>• PolyTuff® I Liquidtight Conduit</li> </ul>
UPC	783585498003

## Dimensions

Length	100 ft
Trade Size	3/4
Width	1.04 in

## Electrical Ratings

Voltage Rating	600 V
----------------	-------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Meets Requirements Of NEC</li> <li>• UL Listed 1660. Approved For Outdoor And Direct Burial</li> </ul>
----------------------	---

Standards - RoHS Compliance CM Status

## Logistics

Carton Quantity	100
Pallet Quantity	2000

## Product Assets

- [Catalog Page - WDK W-89 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Industrial Solutions](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)

## Related Products

- [H0754 - Kellems Wire Management, Liquidtight System, 45 Degree Male Liquid Tight Connector, 3/4", Steel, Non-Insulated](#)
- [H075 - Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 3/4", Steel, Non-Insulated](#)
- [P075NBKA - Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male Liquid Tight Connector, 3/4", Non-Metallic, Black](#)
- [P0759NBK - Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 3/4", Non-Metallic, Black](#)
- [PS0759NGY - Kellems Wire Management, Liquidtight System, SwivelLok® Multi-Position Male Liquid Tight Connector, 3/4", Non-Metallic, Gray](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-G1075-SPEC-EN | REV 1/2024