



Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1", 100 feet

By Hubbell Wiring Device-Kellems
Catalog # [G1100](#)



Kellems® PolyTuff® I Non-Metallic Liquidtight 1" Conduit, 100 feet.

Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

Application

UL1660

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"> • Electrical - Voltage Rating - 600V Maximum • Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C) • Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C) • Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)
Type	<ul style="list-style-type: none"> • PolyTuff® I Liquidtight Conduit • PolyTuff® I Liquidtight Conduit
UPC	783585333656

Dimensions

Length	100 ft
Trade Size	1
Width	1.30 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Meets Requirements Of NEC • UL Listed 1660. Approved For Outdoor And Direct Burial
----------------------	---

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity	100
Pallet Quantity	2000

Product Assets

- [Catalog Page - WDK W-89 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Industrial Solutions](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)

Related Products

- [P100NGYA - Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male Liquid Tight Connector, 1", Non-Metallic, Gray](#)
- [PS1009NBK - Kellems Wire Management, Liquidtight System, SwivelLok® Multi-Position Male Liquid Tight Connector, 1", Non-Metallic, Black](#)
- [H10091 - Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 1", Steel, Insulated](#)
- [P1009NBK - Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid-Tight Connector, 1", Non-Metallic, Black](#)
- [H1001 - Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1", Steel, Insulated](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-G1100-SPEC-EN | REV 1/2024