



# Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet

By Hubbell Wiring Device-Kellems  
Catalog # [G1125](#)



Kellems® Liquidtight System, Non-Metallic PolyTuff® I Conduit,  
1-1/4", 100 feet.

## Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

## Application

UL1660

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Performance	<ul style="list-style-type: none"> <li>• Electrical - Voltage Rating - 600V Maximum</li> <li>• Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)</li> <li>• Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)</li> <li>• Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)</li> </ul>
Type	<ul style="list-style-type: none"> <li>• PolyTuff® I Liquidtight Conduit</li> <li>• PolyTuff® I Liquidtight Conduit</li> </ul>
UPC	783585333663

## Dimensions

Length	100 ft
Trade Size	1 1/4
Width	1.65 in

## Electrical Ratings

Voltage Rating	600 V
----------------	-------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Meets Requirements Of NEC</li> <li>• UL Listed 1660. Approved For Outdoor And Direct Burial</li> </ul>
----------------------	---

Standards - RoHS Compliance CM Status

## Logistics

Carton Quantity	100
Pallet Quantity	600

## Product Assets

- [Catalog Page - WDK W-89 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)

## Related Products

- [P125NBK - Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male Liquid Tight Connector, 1 1/4", Non-Metallic, Black](#)
- [H1251 - Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1 1/4", Steel, Insulated](#)
- [H12541 - Kellems Wire Management, Liquidtight System, 45 Male Liquid Tight Connector, 1 1/4", Steel, Insulated](#)
- [P1259NBK - Kellems Wire Management, Liquidtight System, PolyTuff® 90 Degree Male Liquid Tight Connector, 1 1/4", Non-Metallic, Black](#)
- [H1259 - Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 1 1/4", Steel, Non-Insulated](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-G1125-SPEC-EN | REV 1/2024