

Replaced By GFSG5362I - Extra Heavy Duty Industrial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [GF5362SGI](#)



20A, 125V Industrial Grade, Tamper-Resistant, Weather-Resistant, Ground Fault Receptacle

Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

General

Catalog Number	GF5362SGI
EU RoHS Indicator	Contact Manufacturer
Series	Extra Heavy Duty
Type	Tamper-Resistant/Weather-Resistant
UPC	783585581071

Electrical Ratings

Current / Amperage Rating	20 A
---------------------------	------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GF5362SGI AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2825_INSTALLINST](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_GF5362SG_DRAWING_PDF](#)
- [Specifications - GF5362SGI Specification Sheet English](#)
- [Specifications - WIRING_GF5362SGI_spec](#)
- [Specifications - GF5362SGI](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)