

GF5362SGR

Par Hubbell Wiring Device-Kellems

No de catalogue [GF5362SGR](#)

20A, 125V de qualité industrielle, inviolable, résistant aux intempéries, prise pour défaut de terre.



Caractéristiques

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

Général

Catalog Number	GF5362SGR
Couleur	Rouge
Indicateur EU RoHs	Contact Manufacturer
Série	Extra Heavy Duty
Type	Tamper-Resistant/Weather-Resistant
UPC	783585581118

Caractéristiques électriques

Courant nominal 20 A

Logistique

Quantité dans l'emballage 10

Documentation

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GF5362SGR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2825_INSTALLINST](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_GF5362SG_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Autoguard GFCI Receptacles](#)
[Video - Tamper-Resistant Receptacles](#)

