

Replaced By GFSG8200I - Extra
Heavy Duty Hospital Grade Tamper-
Resistant/Weather Resistant
AUTOGUARD® Self-Test GFCI
Receptacle, 15A, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [GF8200SGI](#)



15A, 125V Industrial Hospital Grade, Tamper-Resistant, Weather-Resistant, Ground Fault Receptacle

Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

General

Catalog Number	GF8200SGI
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Type	Tamper-Resistant/Weather-Resistant
UPC	783585581132

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GF8200SGI AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2825_INSTALLINST](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Sales Drawings - WDK_GF8200SG_DRAWING_PDF](#)
- [Specifications - GF8200SGI Specification Sheet French](#)
- [Specifications - WIRING_GF8200SGI_spec](#)
- [Specifications - GF8200SGI Specification Sheet English](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)