

Replaced By GFSG8300R - Extra Heavy Duty Hospital Grade Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Red

By Hubbell Wiring Device-Kellems
Catalog # [GF8300SGR](#)

20A, 125V Industrial Hospital Grade, Tamper-Resistant, Weather-Resistant, Ground Fault Receptacle

Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

General

Catalog Number	GF8300SGR
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Type	Tamper-Resistant/Weather-Resistant
UPC	783585581231

Electrical Ratings

Current / Amperage Rating	20 A
---------------------------	------



Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GF8300SGR AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2825_INSTALLINST](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Sales Drawings - WDK_GF8300SG_DRAWING_PDF](#)
- [Specifications - GF8300SGR Specification Sheet English](#)
- [Specifications - WIRING_GF8300SGR_spec](#)
- [Specifications - GF8300SGR](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)