

GFHW13125

By Hubbell Wiring Device-Kellems
Catalog # [GFHW13125](#)

Hard Wired GFCI, Industrial/Commercial, 120V AC Output, 30A
120V AC, 4-6 mA Trip Level



Application

Wire Into Circuit

General

Catalog Number	GFHW13125
Color	Black, Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Thermoplastic
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
UPC	783585005355

Dimensions

Weight	1.6 lb
--------	--------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Hard Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120 VAC

Conductor Related

Conductor Size	Use #10 AWG Minimum
----------------	---------------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFHW13125 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1827_INSTALLINST](#)
[Sales Drawings - WDK_GFHW13_DRAWING_PDF](#)
[Specifications - GFHW13125 Specification Sheet French](#)
[Specifications - GFHW13125 Specification Sheet English](#)