

GFHW33005

By Hubbell Wiring Device-Kellems
Catalog # [GFHW33005](#)

Hard Wired GFCI, Industrial/Commercial, No Output, 30A
120/240V AC, 4-6 mA Trip Level



Application

Wire Into Circuit

General

Catalog Number	GFHW33005
Color	Black, Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Thermoplastic
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
UPC	783585005225

Dimensions

Weight	1.6 lb
--------	--------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Hard Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120/240 VAC

Conductor Related

Conductor Size	Use #10 AWG Minimum
----------------	---------------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFHW33005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1827_INSTALLINST](#)
- [Sales Drawings - WDK_GFHW33_DRAWING_PDF](#)
- [Specifications - GFHW33005 Specification Sheet English](#)
- [Specifications - GFHW33005 Specification Sheet French](#)