

GFP2305

By Hubbell Wiring Device-Kellems
Catalog # [GFP2305](#)

GFCI High Amperage Portables, Industrial/Commercial, Manual
Set, 30A 240V AC, 6' Cord, 4-6 mA Trip Level



Application

Line Cord Only No Devices

General

Catalog Number	GFP2305
Color	Black, Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
UPC	783585005652

Dimensions

Outside Diameter	0.335
Weight	3.15 lb

Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	240 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD1827_INSTALLINST](#)
- [Sales Drawings - WDK_GFP23_DRAWINGS_PDF](#)
- [Specifications - GFP2305 Specification Sheet French](#)
- [Specifications - GFP2305 Specification Sheet English](#)