

Portable GFCI Line Cord Twist-Lock®

By Hubbell Wiring Device-Kellems
Catalog # [GFPILST20250LKA](#)

Circuit Guard® Heavy Duty GFCI Line Cord, Twist-Lock®, Automatic Set, 20A, 250V AC, L6-20, 2', 12/3 SJTW.



Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- IP69K GFCI housing for use in harsh environments
- Self-test functionality in accordance with UL 943

Application

Heavy Duty Industrial

General

Catalog Number	GFPILST20250LKA
Environmental Conditions	Indoor, Outdoor, Wahsdown
Material	Non-Metallic
Number Of Poles	2
Series	Extra Heavy Duty
Style	Automatic Set
Temperature Rating	-31°F to 150°F (-35°C to 66°C)
Type	Locking
UPC	783585694481

Electrical Ratings

Amperage Rating	20 A
Phase	1 PH
Voltage Rating	250 VAC

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	UL 943
----------------------	--------

Product Assets

- [Catalog Page - WDK K-16 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2165](#)
- [Sales Drawings - M14318](#)
- [Specifications - GFPILST20250LKA Specification Sheet](#)
- [Specifications - WIRING_GFPILST20250LKA_spec](#)
- [Specifications - GFPILST20250LKA Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)