

Portable GFCI 30A Line Cord

By Hubbell Wiring Device-Kellems
Catalog # [GFPST2302](#)

Extra Heavy Duty Industrial Circuit Guard® Portable GFCI, 30A, 240V AC, 25' Cord Length, 10/3 SJGOOW, Type 4X, 4-6mA Trip Level, Manual Set, Black



Features

- High impact UV stabilized housing for long life
- TYPE 4x and 6P wet location rated for indoor/outdoor applications
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Application

Heavy Duty Industrial

General

Catalog Number	GFPST2302
Environmental Conditions	Indoor, Outdoor, Wahsdown
Material	Non-Metallic
Number Of Poles	2
Series	Extra Heavy Duty
Style	Manual Set
Temperature Rating	-31°F to 150°F (-35°C to 66°C)
Type	Portable
UPC	783585703046

Electrical Ratings

Amperage Rating	30 A
Phase	1 PH
Voltage Rating	240 VAC

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	UL 943
----------------------	--------

Product Assets

- [Catalog Page - WDK K-19 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD3026](#)
- [Sales Drawings - M14317](#)
- [Specifications - GFPST2302 Specification Sheet](#)
- [Specifications - GFPST2302 Specification Sheet French](#)
- [Specifications - WIRING_GFPST2302_spec](#)
- [Warranty - Industrial & Commercial Products](#)