

Heavy Duty Hospital Grade
AUTOGUARD® Self-Test GFCI
Receptacle, 20A, Brown

By Hubbell Wiring Device-Kellems
Catalog # [GFR83](#)



Straight Blade Devices, Receptacle, GFCI, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown

Features

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction

Application

- Commercial Hospital Grade

General

Catalog Number	GFR83
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Brass • Power Contacts - Brass
Style	Standard
UPC	883778999222

Dimensions

Height	4.12 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Wire Size	#14 - #10 AWG
-----------	---------------

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-15 Catalog Page](#)
- [Catalog Page - WDK K-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14627_ACAD](#)
- [Installation Manuals - PD2987](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles CA](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFR83](#)
- [Specifications - GFR83 Specification Sheet](#)
- [Specifications - Wiring GFR83 specification sheet](#)
- [Warranty - Industrial & Commercial Products](#)