



Wiring Device-Kellems

GFRST20SNAPLA

By Hubbell Wiring Device-Kellems
Catalog # [GFRST20SNAPLA](#)

SNAP-Connect GFCI Receptacle, 20A, AUTOGUARD, Self Test, 125V, 2-Pole 3-Wire Grounding, 5-20R.



Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

Application

Commercial Grade

General

Color	<ul style="list-style-type: none"> • Light Almond • Amande pâle
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Item Type	Style Line GFCI Receptacle
Material	Nylon
Series	Heavy Duty
Style	Standard
Type	<ul style="list-style-type: none"> • Standard • Standard
UPC	883778124556

Dimensions

Dimensions	3.28 in x 1.77 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.77 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Wire Size #12 AWG

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - WDK A-18 Catalog Page](#)
- [Catalog Page - WDK K-5 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - GFRST20SNAPLA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2484_INSTALLINST](#)
- [Literature - SNAPConnect® Devices](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Sales Drawings - WDK_GFRST20SNAP_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - SNAPConnect Devices](#)

Related Products

[SNAPIRA](#)



A proud member of the Hubbell Family.

