

Dispositifs de protection de
l'alimentation, prise, auto-test,
DDFT, 20A 125V, 2-pôles 3-fils avec
terre, 5-20R, blanc

Par Hubbell Wiring Device-Kellems
No de catalogue [GFRST20W](#)

Prise DDFT 20A à auto-vérification, Mise à la terre 2 pôles 3 fils,
5-20R, Blanc.



Caractéristiques

- Technologie autotest brevetée AUTOGUARD®
- Pince de câblage arrière interne et guide pour une terminaison rapide et sécurisée
- Construction triple essuyage

Général

Catalog Number	GFRST20W
Couleur	• White • Blanc
Indicateur EU RoHs	Contact Manufacturer
Série	Heavy Duty
Type	Standard
Type	Standard
UPC	883778122156

Caractéristiques électriques

Courant nominal	20 A
Courant nominal	20 A
Description de la tension nominale	125 V

Certifications et conformité

Classe NEMA nominale	5-20R
Norme(s) de l'industrie	Meets All NEC® Requirements

Logistique

Nombre d'unités sur la palette	2240
Quantité dans l'emballage	10

Documentation

[Catalog Page - WDK K-5 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFRST20W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2082_INSTALLINST](#)
[Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
[Literature - Health Screening Power Solutions](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Sales Drawings - WDK_GFRST20W_DRAWINGS_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Autoguard GFCI Receptacles](#)