



Wiring Device-Kellems

GFRST82BKNL

By Hubbell Wiring Device-Kellems
Catalog # [GFRST82BKNL](#)

Straight Blade Devices, Receptacle, GFCI, Commercial Hospital Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black, With Light Light.



Features

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Includes light sensor controls for automatic on and off, custom dual lens for optimum light output

General

Color	<ul style="list-style-type: none"> • Black • Noir
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Style	Nightlight
Type	<ul style="list-style-type: none"> • Standard • Standard
UPC	783585485911

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-15 Catalog Page](#)
- [Catalog Page - WDK K-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - GFRST82BKNL AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2082_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Sales Drawings - WDK_GFRST82BKNL_DRAWINGS_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)



A proud member of the Hubbell Family.