

GFRST82R

Par Hubbell Wiring Device-Kellems
No de catalogue [GFRST82R](#)

Prise DDFT 15A de qualité hospitalière, Styleline, 125V, face affleurante, rouge.



Caractéristiques

- Indicateur d'alimentation vert et indicateur de déclenchement rouge
- Technologie d'autotest brevetée AUTOGUARD®
- Construction à triple essuyage

Général

Catalog Number	GFRST82R
Couleur	<ul style="list-style-type: none">• Red• Rouge
Indicateur EU RoHs	Contact Manufacturer
Série	Hospital Grade
Type	Standard
Type	Standard
UPC	783585485164

Caractéristiques électriques

Courant nominal	15 A
Description de la tension nominale	125 V

Certifications et conformité

Classe NEMA nominale	5-15R
Norme(s) de l'industrie	Meets All NEC® Requirements

Logistique

Quantité dans l'emballage	10
---------------------------	----

Documentation

[Catalog Page - WDK L-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFRST82R AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2082_INSTALLINST](#)
[Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
[Literature - Duct Products Guide](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Sales Drawings - WDK_GFRST82_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Autoguard GFCI Receptacles](#)

