

GFRST83ALNL

Par Hubbell Wiring Device-Kellems

No de catalogue [GFRST83ALNL](#)

Straight Blade Devices, Receptacle, GFCI, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Almond , With Night Light.



Caractéristiques

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Includes light sensor controls for automatic on and off, custom dual lens for optimum light output
- Indicateur d'alimentation vert et indicateur de déclenchement rouge
- Technologie brevetée d'autotest AUTOGUARD®
- Construction à triple essuyage
- Comprend des commandes de capteur de lumière pour l'allumage et l'extinction automatiques, une double lentille personnalisée pour une luminosité optimale.

Général

Numéro de catalogue	GFRST83ALNL
Couleur	
Série	Classe d'hôpital
Style	Veilleuse
Type	Standard
CUP	783585485980

Caractéristiques électriques

Courant / Intensité nominale	20 A
Tension nominale Description	125 V

Certifications et conformité

Norme(s) industrielle(s)	Répond à toutes les exigences de la NEC®.
Nema Rating	5-20R

Logistique

Quantité de cartons	10
---------------------	----

Documentation

- [Catalogues - WDK Catalog Full 2024](#)
- [Dessin technique - GFRST83ALNL AutoCAD Drawing](#)
- [Dessins de vente - WDK_GFRST83_DRAWINGS_PDF](#)
- [Littérature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Littérature - Duct Products Guide](#)
- [Manuels d'installation - WIRING_PD2082_INSTALLINST](#)
- [Spécifications - GFRST83ALNL](#)
- [Spécifications - Wiring GFRST83ALNL Specification Sheet](#)