



Wiring Device-Kellems

# GFRST83SNAP

By Hubbell Wiring Device-Kellems  
Catalog # [GFRST83SNAP](#)

SNAP-Connect Straight Blade GFCI Receptacle, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.



## Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

## Application

Commercial Hospital Grade

## General

Color	<ul style="list-style-type: none"> <li>• Brown</li> <li>• Brun</li> </ul>
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Style	Standard
Type	<ul style="list-style-type: none"> <li>• Standard</li> <li>• Standard</li> </ul>
UPC	783585486345

## Dimensions

Dimensions	3.28 in x 1.77 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.77 in

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Wire Size #12 AWG

## Certifications and Compliance

Industry Standard(s) Meets All NEC® Requirements  
Nema Rating 5-20R

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - WDK A-17 Catalog Page](#)
- [Catalog Page - WDK L-5 Catalog Page](#)
- [Catalog Page - WDK L-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - GFRST83SNAP AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2484\\_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Sales Drawings - WDK\\_GFRST83SNAP\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - SNAPConnect Devices](#)

## Related Products

[SNAP1RA](#)



A proud member of the Hubbell Family.

