

Power Protection Devices,
Receptacle, Self Test, GFCI, TRWR,
Commercial Grade, 15A 125V, 2-Pole
3-Wire Grounding, 5-15R, Black

By Hubbell Wiring Device-Kellems
Catalog # [GFRTW15BLK](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TRWR,
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,
Black

General

Catalog Number	GFRTW15BLK
Color	Black
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant, Weather Resistant
UPC	883778999284

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFRTW15BLK AutoCAD Drawing](#)
- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Installation Manuals - PD2987](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Sell Sheets - Commercial GFCI- French](#)
- [Sell Sheets - Commercial GFCI- English](#)
- [Specifications - GFRTW15BLK Specification Sheet English](#)
- [Specifications - WIRING_GFRTW15BLK_spec](#)
- [Specifications - GFRTW15BLK](#)