

Power Protection Devices,
Receptacle, Self Test, GFCI, TRWR,
Commercial Grade, 15A 125V, 2-Pole
3-Wire Grounding, 5-15R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [GFRTW15I](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TRWR,
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,
Ivory

Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

Catalog Number	GFRTW15I
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant, Weather Resistant
UPC	883778999314

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFRTW15I AutoCAD Drawing](#)
- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Installation Manuals - PD2987](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Sell Sheets - Commercial GFCI- French](#)
- [Sell Sheets - Commercial GFCI- English](#)
- [Specifications - GFRTW15I](#)
- [Specifications - WIRING_GFRTW15I_spec](#)
- [Specifications - GFRTW15I Specification Sheet English](#)