

Replaced By GFTR15BLK - Heavy
Duty Commercial Tamper-Resistant
AUTOGUARD® Self-Test GFCI
Receptacle, 15A, Black

By Hubbell Wiring Device-Kellems
Catalog # [GFTRST15BK](#)

Power Protection Devices, Receptacle, Self Test, GFCI,
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R,
Black

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Catalog Number	GFTRST15BK
Color	Black
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
UPC	883778122255

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V



Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	2400

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFTRST15BK AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2082_INSTALLINST](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - Residential Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Sales Drawings - WDK_GFTRST15BK_DRAWINGS_PDF](#)
- [Specifications - GFTRST15BK Specification Sheet](#)
- [Specifications - Wiring GFTRST15BK Specification Sheet](#)
- [Specifications - GFTRST15BK](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)