

Replaced By GFRTW15W - Heavy Duty
Commercial Weather Resistant
AUTOGUARD® Self-Test GFCI Receptacle,
15A, White

By Hubbell Wiring Device-Kellems
Catalog # [GFTWRST15W](#)

Power Protection Devices, Receptacle, Self Test, GFCI, TRWR,
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,
White Almond

Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Specifications

EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15R
Industry Standard(s)	Meets All NEC® Requirements

Current

Amperage Rating	15 A
-----------------	------

General

Color	White
Style	Standard
Specifications	• Base - Nylon



- Face - Nylon
 - Ground Contacts - Brass
 - Mounting Screws - Zinc plated steel
 - Mounting Strap - Zinc plated steel
 - Power Contacts - Brass
- UPC
Type
- 883778122637
Tamper-Resistant, Weather Resistant

Logistics

Pallet Quantity	2240
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)