

Replaced By GFRTW83 - Heavy
Duty Hospital Grade Tamper-
Resistant/Weather Resistant
AUTOGUARD® Self-Test GFCI
Receptacle, 20A, Brown

By Hubbell Wiring Device-Kellems
Catalog # [GFTWRST83](#)



Straight Blade Devices, Receptacle, GFCI, Tamper and Weather
Resistant, Commercial Hospital Grade, Self Test, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Brown

General

Catalog Number	GFTWRST83
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Brass • Power Contacts - Brass
Style	Standard
UPC	783585485386

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
----------------------	-----------------------------

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-14 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFTWRST83 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2082_INSTALLINST](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - Duct Products Guide](#)
- [Sales Drawings - WDK_GFTWRST83_DRAWINGS_PDF](#)
- [Specifications - GFTWRST83 Specification Sheet](#)
- [Specifications - GFTWRST83](#)
- [Specifications - Wiring GFTWRST83 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)