



Wiring Device-Kellems

GFTWRST83W

By Hubbell Wiring Device-Kellems
Catalog # [GFTWRST83W](#)

Straight Blade Devices, Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White.



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Color	<ul style="list-style-type: none"> • White • Blanc
EU RoHS Indicator	Contact Manufacturer
Series	Hospital Grade
Style	Standard
Type	<ul style="list-style-type: none"> • Tamper-Resistant, Weather Resistant • Tamper-Resistant, Weather Resistant
UPC	783585485416

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK L-14 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - GFTWRST83W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2082_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - WDK_GFTWRST83_DRAWINGS_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)



A proud member of the Hubbell Family.