



Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Double Pole, 20A 120/277V AC, Back and Side Wired Toggle

By Hubbell Wiring Device-Kellems
Catalog # [HBL1222I](#)



HBL® Extra Heavy Duty Industrial 20A Double Pole Switch, 120/277V, Back and Side Wired.

Features

- Large brass binding head screws with deep slots
- Abuse resistant nylon toggle
- Strip gauge for accurate wiring

Application

Back and Side Wired

General

Color	<ul style="list-style-type: none"> • Ivory • Ivoire
Number Of Poles	Double Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute • Electrical - Max. Continuous Current - 20A • Electrical - Max. Working Voltage - 277V AC • Electrical - Overload - Minimum 4.8 times rated current for 100 cycles • Electrical - Temperature Rise - 30°C maximum at rated current • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact • Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

Series Extra Heavy Duty
Style Double Pole

Dimensions

Dimensions	4.06 in x 1.31 in x 1.87 in
Height	1.87 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK D-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL1222I AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1242_INSTALLINST](#)
[Sales Drawings - WDK_HBL1222_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Type

- Toggle
- Toggle

UPC

783585431642



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL1222I-SPEC-EN | REV 1/2024