



# Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Double Throw Center Off, 10A 250V/10A 125V,

By Hubbell Wiring Device-Kellems  
Catalog # [HBL123](#)



Switches and Lighting Controls, Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Double Throw Center Off, 10A 250V/10A 125V,.

## Features

- Nickel Plated for Corrosion Resistance

## General

Action	SPDT
Horsepower - Maximum	0.75
Item Type	Panel Mount and Bat Handle Switch
Mounting Method	Panel Mount
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Environmental - Operating Temperatures - Max Continuous- 75 °C, Minimum -40 °C Without Impact
Series	Single Pole/Double Throw
Style	Screw Terminal
Type	<ul style="list-style-type: none"><li>• General Purpose</li><li>• General Purpose</li></ul>
UPC	783585016764

## Dimensions

Dimensions	2.15 in x 0.56 in x 1.12 in
Height	1.12 in
Length	2.15 in
Weight	0.05 lb
Width	0.56 in

## Electrical Ratings

Amperage Rating	10/20 A
Connectivity	Screw Terminals
Current / Amperage Rating	10/20 A
Voltage Rating	250/125 VAC

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK D-20 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL123 AutoCAD Drawing](#)  
[Sales Drawings - WDK\\_HBL123\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL123-SPEC-EN | REV 1/2024