



# Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1372](#)

Circuit-Lock® NEMA 1 Enclosure Toggle Switch Disconnect, 2-Pole, 30A 600V AC, Aluminum.



## Features

- All aluminum cover and base
- Base is pre-drilled for rear surface mounting
- Wiring conduit knockouts
- ½" and ¾" NPT
- Top, bottom or back wire entry points
- Surface mount control
- Switch can be locked in the OFF position as a method of compliance with OSHA lockout/tagout

## Application

Standard Toggle

## General

Enclosure Type	NEMA 1
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	20
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute</li> <li>• Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load</li> <li>• Electrical - Max. Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94HB/VO</li> <li>• Environmental - Operating Temperature - Max. 75°C, Min. -40°C continuous w/o impact</li> <li>• Mechanical - Mechanical Life - Min. 10,000 minimum cycles</li> <li>• Mechanical - Switch Rating - 25 inch pounds</li> <li>• Mechanical - Terminal Accommodations - #10 AWG Max</li> <li>• Mechanical - Terminal</li> </ul>

## Dimensions

Dimensions	4.52 in x 3.2 in x 3.15 in
Display Size	Standard Sized Product
Height	3.15 in
Length	4.52 in
Weight	1.05 lb
Width	3.2 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Single Phase
Wattage	18000 W

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA-C22.2 No.14 Industrial Control File LR-46186</li> <li>• UL 508, Industrial Control File #E70402</li> </ul>
----------------------	---

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK F-22 Catalog Page](#)
- [Catalog Page - WDK F-24 Catalog Page](#)
- [Catalog Page - WDK F-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING\\_PD2018\\_INSTALLINST](#)
- [Literature - WLFDS011-CANFR](#)
- [Literature - WLFDS011-CANEN](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - 30A Manual Motor Controllers](#)
- [Sales Drawings - WDK\\_HBL1372\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Torque - 20 inch pounds

- Mechanical - Wire Type - Solid and stranded copper wire only

Series

Non-Fused

Style

Standard Duty

Type

- Disconnect Switches
- Disconnect Switches

UPC

783585680897



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL1372-SPEC-EN | REV 1/2024