

Switches and Lighting Controls,
Industrial Grade, Toggle Switches,
Motor Disconnects, Three Pole, 30A
600V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL1379D](#)

Switches and Lighting Controls, Industrial Grade, Toggle
Switches, Motor Disconnects, Three Pole, 30A 600V AC

Features

- Optional Side Guard for close wall applications
- Switch can be locked in the off position
- Thermoset body provides resistance to electrical arc tracking

Application

Standard Toggle

Performance

- Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94HB/VO
- Environmental - Operating Temperature - Max. 75°C,Min. -40°C continuous w/o impact
- Mechanical - Mechanical Life - Min. 10,000 minimum cycles
- Mechanical - Switch Rating - 25 inch pounds
- Mechanical - Terminal Accommodations - #10 AWG Max
- Mechanical - Terminal Torque - 20 inch pounds
- Mechanical - Wire Type - Solid and stranded copper wire only

General

Catalog Number	HBL1379D
Color	Aluminum
EU RoHS Indicator	Yes
Enclosure Type	NEMA 1
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	15
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	Enclosure Material - Aluminum
Style	Standard Duty
Type	Disconnect Switches



UPC 783585202617

Dimensions

Dimensions	4.52 in x 3.2 in x 3.15 in
Display Size	Standard Sized Product
Height	3.15 in
Length	4.52 in
Weight	1.05 lb
Width	3.2 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Three Phase
Wattage	18000 W

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA-C22.2 No.14 Industrial Control File LR-46186• UL 508, Industrial Control File #E70402
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK F-22](#) [Catalog Page - WDK F-24](#) [Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL1379 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2018_INSTALLINST](#)
[Literature - Safety Product Guide](#)
[Literature - Circuit-Lock® Motor Disconnects](#)

Literature - Wiring Device Solutions for Strategic Manufacturing
Facilities
Sales Drawings - WDK_HBL1379_DRAWING_PDF
Specifications - HBL1379D Specification Sheet French

Specifications - HBL1379D Specification Sheet
Specifications - HBL1379D
Specifications - Wiring HBL1379 Specification Sheet



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-HBL1379D-SPEC-EN | REV 4/2025