



Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black, In NEMA 1 Non Metallic Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBL1392](#)



Circuit-Lock® NEMA 1 Enclosure Toggle Switch Disconnect, 2-Pole, 30A 600V AC, Thermoplastic.

Features

- Thermoplastic cover on a plated steel base
- Durable, non-conductive cover
- Wiring conduit knockouts
- ½" and ¾" NPT
- Top, bottom or back wire entry points
- Surface mount control
- Switch can be locked in the OFF position as a method of compliance with OSHA lockout/tagout

Application

Standard Toggle

General

Construction	Fabricated
Enclosure Type	NEMA 1
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Performance	<ul style="list-style-type: none"> • Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute • Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94HB/VO • Environmental - Operating Temperature - Max. 75°C, Min. -40°C continuous w/o impact • Mechanical - Mechanical Life - Min. 10,000 minimum cycles • Mechanical - Switch Rating - 25 inch pounds • Mechanical - Terminal

Dimensions

Dimensions	4.52 in x 3.97 in x 3.43 in
Display Size	Standard Sized Product
Height	3.43 in
Length	4.52 in
Weight	1.5 lb
Width	3.97 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Single Phase
Wattage	18000 W

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA-C22.2 No.14 Industrial Control File LR-46186 • UL 508, Industrial Control File #E70402
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK F-22](#) [Catalog Page](#)
[Catalog Page - WDK F-24](#) [Catalog Page](#)
[Catalog Page - WDK F-17](#) [Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL1392](#) [AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2018_INSTALLINST](#)
[Literature - WLFDS011-CANFR](#)
[Literature - WLFDS011-CANEN](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Safety Product Guide](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Literature - 30A Manual Motor Controllers](#)
[Sales Drawings - WDK_HBL1392_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Accommodations - #10 AWG Max
- Mechanical - Terminal Torque - 20 inch pounds
- Mechanical - Wire Type - Solid and stranded copper wire only

Series
Style
Type

Non-Fused
Standard Duty

- Disconnect Switches
- Disconnect Switches

UPC

783585680927



A proud member of the Hubbell Family.