



Wiring Device-Kellems

# Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Aluminum, NEMA 3R Enclosure with Switch

By Hubbell Wiring Device-Kellems  
Catalog # [HBL13R92](#)



Circuit-Lock® NEMA 3R Enclosure Switch Disconnect, 2-Pole, 30A 600V AC, Aluminum.

## Features

- All aluminum cover and base
- Flip-lid enclosure
- Ideal for use on outdoor equipment
- Surface mount control

## Application

Red Slide

## General

Enclosure Type	NEMA 3R
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Series	Non-Fused
Style	Standard Duty
Type	<ul style="list-style-type: none"> <li>• Disconnect Switches</li> <li>• Disconnect Switches</li> </ul>
UPC	783585680989

## Dimensions

Dimensions	5.52 in x 4.4 in x 3.3 in
Display Size	Standard Sized Product
Height	3.3 in
Length	5.52 in
Weight	1.45 lb
Width	4.4 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Wattage	18000 W

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets

- [Catalog Page - WDK F-24](#)
- [Catalog Page - WDK F-23](#)
- [Catalog Page - WDK F-17](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL13R92 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2018\\_INSTALLINST](#)
- [Literature - WLFDS011-CANFR](#)
- [Literature - WLFDS011-CANEN](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Safety Product Guide](#)
- [Literature - 30A Manual Motor Controllers](#)
- [Sales Drawings - WDK\\_HBL13R92\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.