



Wiring Device-Kellems

# Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6' Length, Gray



By Hubbell Wiring Device-Kellems  
Catalog # [HBL20GBA612GY](#)

Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6' Length, Gray.

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gray</li> </ul>
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	6
Performance	<ul style="list-style-type: none"> <li>• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R</li> <li>• Mechanical - Wire - #12 AWG Stranded Copper</li> </ul>
Series	Metal
Style	Standard
Type	<ul style="list-style-type: none"> <li>• Two Circuits</li> <li>• Two Circuits</li> </ul>
UPC	783585214740

## Dimensions

Length	6 ft
--------	------

## Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

## Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Standard C22.2 no. 62</li> <li>• E253976 /E253830 /E253833</li> <li>• UL Standard UL 5</li> </ul>
----------------------	--

## Logistics

Carton Quantity	2
-----------------	---

## Product Assets

- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL20GBA612GY AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2473\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_HBL20GBA612\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.