

Locking Devices, Hubbellock,
Hospital Use, Flush Receptacle, 20A
125V, 2-Pole 3-Wire Grounding,
Non-NEMA, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL23000HG](#)



Locking Devices, Hubbellock, Hospital Use, Flush Receptacle,
20A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal,
Black

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Thermoset molded housing provides maximum heat resistance

General

Catalog Number	HBL23000HG
Color	Black
EU RoHS Indicator	No
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	Material - Phenolic
UPC	783585015712

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A

Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - WDK L-17 Catalog Page](#)
[Catalog Page - WDK N-18 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1184_INSTALLINST](#)
[Literature - Healthcare Product Solutions](#)
[Literature - Duct Products Guide](#)
[Sales Drawings - WDK_HBL23000HG_DRAWING_PDF](#)
[Specifications - HBL23000HG Specification Sheet French](#)
[Specifications - HBL23000HG Specification Sheet English](#)
[Specifications - WIRING_HBL23000HG_spec](#)
[Warranty - Industrial & Commercial Products](#)