



# Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, L5-20R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2313BK](#)



Twist-Lock® Industrial 20A Female Connector, 125V, 2-Pole, 3-Wire Grounding, NEMA L5-20R Nylon.

## Features

- All black ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.
- Ribbed nylon housing provides a secure grip and impact and chemical resistance

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	20A Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Moisture Resistance - IP20</li> </ul>

## Dimensions

Dimensions	2.26 in x 2.26 in x 3.86 in
Display Size	Standard
Height	3.86 in
Length	2.26 in
Weight	0.35 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Range	0.360 - 0.930 in
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Catalog Page - WDK B-21 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL2313BK AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2128\\_INSTALLINST](#)  
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Sales Drawings - WDK\\_HBL\\_2313\\_DRAWING\\_PDF](#)

Temperatures - w/ 20

Suitability

- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

[Sales Drawings - WDK\\_HBL2313\\_DRAWING\\_PDF](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

[Video - Twist-Lock Devices](#)

Temperature Rating

Maximum continu : 75° C ;  
Minimum continu : -40° C sans impact, -25° avec impact.

Type

- Connector Body
- Connector Body

UPC

783585172194



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL2313BK-SPEC-EN | REV 1/2024