

EdgeConnect™ Twist-Lock® Receptacle with Spring Termination, 20A, 125/250V, L14, 20R, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL2410ST](#)

EdgeConnect™ Twist-Lock® Receptacle, 20A 125/250V, L14-20R, BK, with Spring Termination.



Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

General

Catalog Number	HBL2410ST
Item Type	30A, 125/250V Twist-Lock Receptacle with Spring Termination
Number Of Poles	3
UPC	783585788593

Dimensions

Dimensions	3.28 in x 1.7 in x 1.468 in
Height	1.468 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	125/250 V

Conductor Related

Number Of Wires	4
Wire Size	14 AWG - 10 AWG solid, 14 AWG - 8 AWG stranded (including compact stranded)

Logistics

Carton Quantity 30

Product Assets

[3D Product View - Twist-Lock® EdgeConnect HBL2320ST Receptacle AR Model](#)
[Brochures - EdgeConnect Brochure](#)
[Brochures - Twist-Lock Edge Series French](#)
[Brochures - Twist-Lock Edge Series](#)
[Brochures - EdgeConnect Brochure French](#)
[Catalog Page - WDK B-35 Catalog Page](#)
[Catalog Page - WDK B-27 Catalog Page](#)
[Catalog Page - WDK B-23 Catalog Page](#)
[Catalog Page - WDK B-33 Catalog Page](#)
[Catalog Page - WDK B-31 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M14074_ACAD](#)
[Installation Manuals - PD2880](#)
[Literature - Healthcare Product Solutions](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - Twist-Lock® Edge Series Devices](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - M14074](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Twist-Lock® Edge Plugs and Inlets](#)
[Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)
[Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL2410ST-SPEC-EN | REV 6/2024