



Wiring Device-Kellems

EdgeConnect™ Twist-Lock® Plug with Spring Termination, 20A, 125/250V, L14, 20P, Black and White Nylon

By Hubbell Wiring Device-Kellems
Catalog # [HBL2411ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 125/250V AC, 3- Pole 4-Wire Grounding, L14-20P, Spring Terminal, Black and White Nylon.

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination
- Superior cord grip design protects terminations from excess strain

General

Item Type	Plug
Number Of Poles	4
Series	EdgeConnect™
UPC	783585681573

Electrical Ratings

Current Rating	20 A
Voltage Rating	125/250 VAC

Conductor Related

Number Of Wires 5

Logistics

Carton Quantity 30

Product Assets

- [Brochures - H3677-WLBL005_Twist-Lock Edge Series-cdn](#)
- [Brochures - H3678-FR_Twist-Lock Edge Series](#)
- [Catalog Page - WDK B-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - PD2973](#)
- [Literature - EdgeConnect™ Technology \(EP-WDK-MFG-BR-EN-01348\)](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - M14339](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL2411ST-SPEC-EN | REV 1/2024