

EdgeConnect™ Twist-Lock®,  
Female Connector Body, 20A  
125/250V, Screwless Terminal,  
Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2413ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female  
Connector Body, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-  
20R, Screwless Terminal, Black and White

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Superior cord grip design protects terminations from excess strain

General

Catalog Number	HBL2413ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	3
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Connector
UPC	783585719115

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 3,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W- C-596, Certified to CSA C22.2 No.42
Nema Rating	L14-20R

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure French](#)  
[Brochures - EdgeConnect Brochure](#)  
[Catalog Page - WDK B-23 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - PD2973](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Literature - EdgeConnect™ Technology](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)  
[Sales Drawings - M14333](#)  
[Specifications - HBL2413ST Specification Sheet](#)  
[Specifications - Wiring HBL2413ST specification sheet](#)  
[Specifications - HBL2413ST Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)