



Wiring Device-Kellems

EdgeConnect™ Twist-Lock® Flanged Inlet with Spring Termination, 20A, 125/250V, L14, 20P, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2415ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 125/250V AC, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, Nylon casing, Back wired, White.

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination
- Backwired termination for ease of installation

General

Item Type	Plug
Number Of Poles	3
Series	EdgeConnect™
UPC	783585681641

Electrical Ratings

Current Rating	20 A
Voltage Rating	125/250 VAC

Conductor Related

Number Of Wires 4

Logistics

Carton Quantity 10

Product Assets

- [Brochures - H3677-WLBL005_Twist-Lock Edge Series-cdn](#)
- [Brochures - H3678-FR_Twist-Lock Edge Series](#)
- [Catalog Page - WDK B-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - PD2974](#)
- [Literature - EdgeConnect™ Technology \(EP-WDK-MFG-BR-EN-01348\)](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_M-14340_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL2415ST-SPEC-EN | REV 1/2024