

Locking Devices, Twist-Lock®,
Single Flush Receptacle, 20A, 250V
AC, 3-Pole, 4-Wire Grounding,
Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL2420RT](#)

Locking Devices, Twist-Lock®, Single Flush Receptacle, 20A,
250V AC, 3-Pole, 4-Wire Grounding, Black

Features

- Accepts ring terminals
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Application

Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2420RT
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	20A Single Flush Receptacles
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - Glass-Reinforced thermoplastic polyester (RTP)



- Contacts - Brass
- Face - Nylon
- Mounting Strap - Brass
- Terminal Screws - #10 - 32 Brass

UPC

783585234458

Dimensions

Dimensions	2.37 in x 1.37 in x 1.23 in
Display Size	Standard Sized Product
Height	1.23 in
Length	2.37 in
Weight	0.3 lb
Width	1.37 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Ring Terminal
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 VAC

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L15-20R

Logistics

Carton Quantity	10
Pallet Quantity	3300

Product Assets

[Catalog Page - WDK B-23 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Installation Manuals - WIRING_PD1970_INSTALLINST](#)

[Sales Drawings - WDK_HBL2420_DRAWING_PDF](#)

[Specifications - HBL2420RT Specification Sheet](#)

[Specifications - HBL2420RT Specification Sheet French](#)

[Specifications - Wiring HBL2420RT Specification Sheet](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Twist-Lock Devices](#)

[Video - Twist-Lock Devices](#)

[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-HBL2420RT-SPEC-EN | REV 4/2025