

EdgeConnect™ Twist-Lock® Plug
with Spring Termination, 20A, 3P
250V, L15, 20P, Black and White
Nylon

By Hubbell Wiring Device-Kellems
Catalog # [HBL2421ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Male
Insulgrip® Plug, 20A 3-Phase 250V AC, 3-Pole 4-Wire
Grounding, L15-20P, Spring Terminal, Black and White Nylon.

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination
- Superior cord grip design protects terminations from excess strain

General

Catalog Number	HBL2421ST
Item Type	Plug
Number Of Poles	3
Series	EdgeConnect™
UPC	783585681580

Electrical Ratings

Current Rating	20 A
Voltage Rating	3-Phase 250 VAC

Conductor Related

Number Of Wires	4
-----------------	---

Logistics

Carton Quantity 30

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - Twist-Lock Edge Series](#)
- [Brochures - EdgeConnect Brochure](#)
- [Brochures - Twist-Lock Edge Series French](#)
- [Catalog Page - WDK B-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2973](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14339](#)
- [Specifications - HBL2421ST Specification Sheet](#)
- [Specifications - Wiring HBL2421ST specification sheet](#)
- [Specifications - HBL2421ST Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock® Edge Plugs and Inlets](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)

