



# Metal PlugTrak, 20A 125V, 1 Circuit, 10 Receptacle, 6' Length, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [HBL24GB606GY](#)

Metal PlugTrak, 20A 125V, 1 Circuit, 10 Receptacle, 6' Length,  
Gray.

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## General

Color	<ul style="list-style-type: none"><li>• Gray</li><li>• Gray</li></ul>
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	12
Performance	<ul style="list-style-type: none"><li>• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R</li><li>• Mechanical - Wire - #12 AWG Stranded Copper</li></ul>
Series	Metal
Style	Standard
Type	<ul style="list-style-type: none"><li>• Single Circuit</li><li>• Single Circuit</li></ul>
UPC	783585214900

## Dimensions

Length	6 ft
--------	------



## Electrical Ratings

Current / Amperage Rating 20 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul>
----------------------	--

## Logistics

Carton Quantity 2

## Product Assets

[Catalog Page - WDK S-12 Catalog Page](#)  
[Catalog Page - WDK S-51 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL24GB606GY AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2473\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_HBL24GB606\\_DRAWINGS\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL24GB606GY-SPEC-EN | REV 1/2024