

EdgeConnect™ Twist-Lock®,
Female Connector Body, 20A 3-
Phase Wye 120/208V AC, Black and
White,

By Hubbell Wiring Device-Kellems
Catalog # [HBL2513ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female
Connector Body, 20A 3-Phase Wye 120/208V AC, L21-20R,
Screwless Terminal, Black and White

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Superior cord grip design protects terminations from excess strain

General

Catalog Number	HBL2513ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	4
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Connector
UPC	783585719122

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 3,000V minimum
Phase	3-Phase
Voltage Rating	3P 120/ 208 VAC

Conductor Related

Number Of Wires	5
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W- C-596, Certified to CSA C22.2 No.42
Nema Rating	L21-20R

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure French](#)
[Brochures - EdgeConnect Brochure](#)
[Catalog Page - WDK B-27 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD2973](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - Entertainment Product Solution Guide](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M14333](#)
[Specifications - HBL2513ST Specification Sheet](#)
[Specifications - Wiring HBL2513ST specification sheet](#)
[Specifications - HBL2513ST Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)