

EdgeConnect™ Twist-Lock®  
Flanged Inlet with Spring  
Termination, 20A, 120/208V, L21,  
20P, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2515ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20P, Spring Terminal, Nylon casing, Back wired, White.

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination
- Backwired termination for ease of installation

General

Catalog Number	HBL2515ST
Item Type	Plug
Number Of Poles	4
Series	EdgeConnect™
UPC	783585681658

Electrical Ratings

Current Rating	20 A
Voltage Rating	3-Phase Wye 120/208 VAC

Conductor Related

Number Of Wires	5
-----------------	---

Logistics



Carton Quantity 10

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - Twist-Lock Edge Series](#)
- [Brochures - EdgeConnect Brochure](#)
- [Brochures - Twist-Lock Edge Series French](#)
- [Catalog Page - WDK B-26 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2974](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - WDK\\_M-14340\\_DRAWING\\_PDF](#)
- [Specifications - HBL2515ST Specification Sheet French](#)
- [Specifications - Wiring HBL2515ST specification sheet](#)
- [Specifications - HBL2515ST Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)
- [Video - Twist-Lock® Edge Plugs and Inlets](#)