



Wiring Device-Kellems

# EdgeConnect™ Twist-Lock® Flanged Inlet with Spring Termination, 20A, 277/480V, L22, 20P, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2525ST](#)



Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-20P, Spring Terminal, Nylon casing, Back wired, White.

## Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination
- Backwired termination for ease of installation

## General

Item Type	Plug
Number Of Poles	4
Series	EdgeConnect™
UPC	783585681702

## Electrical Ratings

Current Rating	20 A
Voltage Rating	3-Phase Wye 277/480 VAC

## Conductor Related

Number Of Wires 5

## Logistics

Carton Quantity 10

## Product Assets

- [Brochures - H3677-WLBL005\\_Twist-Lock Edge Series-cdn](#)
- [Brochures - H3678-FR\\_Twist-Lock Edge Series](#)
- [Catalog Page - WDK B-26 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - PD2974](#)
- [Literature - EdgeConnect™ Technology \(EP-WDK-MFG-BR-EN-01348\)](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Twist-Lock® Edge Series Devices](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK\\_M-14340\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL2525ST-SPEC-EN | REV 1/2024