



# Twist-Lock® EdgeConnect™ Receptacle with Spring Termination, 30A, 125V

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2610ST](#)

Twist-Lock® EdgeConnect™ Receptacle with Spring Termination, 30A, 125V, L5-30R.



## Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Single Receptacle
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Size	Standard Sized Product
Temperature Rating	Maximum continu 75°C ; Minimum -40°C (sans impact)
UPC	783585569567

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.70 in

## Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	Withstands 2,000V Minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3
Wire Size	14 AWG - 10 AWG solid, 14 AWG - 8 AWG stranded (including compact stranded)

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL Listed To UL 498</li> <li>• CSA Certified to Specification C22.2 No. 42</li> </ul>
Nema Rating	L5-30R

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Brochures - H3677-WLBL005\\_Twist-Lock Edge Series-cdn](#)  
[Brochures - H3678-FR\\_Twist-Lock Edge Series](#)  
[Catalog Page - WDK B-27 Catalog Page](#)  
[Catalog Page - WDK B-29 Catalog Page](#)  
[Catalog Page - WDK B-35 Catalog Page](#)  
[Catalog Page - WDK B-31 Catalog Page](#)  
[Catalog Page - WDK B-23 Catalog Page](#)  
[Catalog Page - WDK B-33 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - M13892\\_ACAD](#)  
[Installation Manuals - PD2880](#)  
[Literature - EdgeConnect™ Technology \(EP-WDK-MFG-BR-EN-01348\)](#)  
[Literature - Healthcare Product Solutions](#)  
[Literature - Twist-Lock® Edge Series Devices](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Sales Drawings - M13892](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Twist-Lock plugs and flanged inlets with EdgeConnect technology install in 10 seconds](#)

## Related Products

[HBL2611 - Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL2610ST-SPEC-EN | REV 1/2024