



Locking Devices, Twist-Lock®, Watertight Safety Shroud, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL2611SW](#)

Twist-Lock® Watertight Safety-Shroud® Male Plug 30A, 125V, 2-Pole, 3-Wire Grounding, NEMA L5-30P, PBT Housing and Clamps/White.

Features

- Impact resistant shroud protects blades against bending and breaking.
- Reduces exposure to arcing when connecting or disconnecting under load.
- Superior cord grip design protects terminations from excess strain.

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Cord Range	0.325"-0.930" (9-24)
Environmental Conditions	Watertight
Horsepower - Maximum	2
Item Type	30A Watertight Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17
- Environmental - Moisture Resistance - Type 4, 4X, 12, IP66 suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal

Dimensions

Dimensions	2.77 in x 2.77 in x 4.40 in
Display Size	Standard Sized
Height	4.40 in
Length	2.77 in
Weight	0.55 lb
Width	2.77 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.325 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L5-30P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK B-28 Catalog Page](#)
[Catalog Page - WDK B-41 Catalog Page](#)
[Catalog Page - WDK C-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL2611SW AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1270_INSTALLINST](#)
[Literature - Wiring Device Solutions for Strategic](#)

Accommodation - #16
AWG - #8 AWG stranded
copper wire only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Plugs
- Plugs

UPC

783585231600

Literature - Wiring Device Solutions for Strategic Manufacturing Facilities
Literature - Entertainment Product Solution Guide
Sales Drawings - WDK_HBL2611SW_DRAWINGS_PDF
Warranty - Industrial & Commercial Products
Video - Insulgrip Twist-Lock and Straight Blade Devices
Video - Twist-Lock Devices

Related Products

HBL2610SW - Locking Devices, Twist-Lock®, Watertight Safety Shroud, Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Gray

WTSS234SS - Twist-Lock® Devices, Watertight Safety Shroud, Size 2 Adapter, 3/4" Stainless Steel

WTSS234 - Twist-Lock® Devices, Watertight Safety Shroud, Size 2 Adapter, 3/4" Aluminum

HBL2613SW - Locking Devices, Twist-Lock®, Watertight Safety Shroud, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal and White



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL2611SW-SPEC-EN | REV 1/2024