



Wiring Device-Kellems

# Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Gray, High Temp Version

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2613F](#)



Twist-Lock® Industrial Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5,Screw Terminal, High Temp Version.

## Features

- Superior cord grip design protects terminations from excess strain
- Clear, funnel shaped wire entry for ease of termination
- Integral dust shield protects wiring chamber from dust or contaminants.

## Application

Heavy Duty Industrial

## General

Color	Gray
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Grounding Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Environmental - Terminal</li> </ul>

## Dimensions

Dimensions	2.26 in x 2.26 in x 3.86 in
Display Size	Standard
Height	3.86 in
Length	2.26 in
Weight	0.40 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Range	0.360 - 0.930 in
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L5-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

- [Catalog Page - WDK B-29 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL2613F AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1651\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_HBL2613\\_DRAWING\\_PDF](#)

	<p>Identification - Terminals identified in accordance with UL 498</p> <ul style="list-style-type: none"> <li>Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.</li> <li>Connector Body</li> <li>Connector Body</li> </ul>
Type	
UPC	783585038780

Warranty - Industrial & Commercial Products  
 Video - Insulgrip Twist-Lock and Straight Blade Devices  
 Video - Twist-Lock Devices

**Related Products**

- HBLTL2CCBL - Twist-Lock Devices, Colored Cord Clamp, Size 2, Blue
- HBL6032 - Weatherproofing Boots, Weatherproof Device Boot, Black
- HBL6031 - Weatherproofing Boots, Weatherproof Device Boot, Black
- HBL2611F - Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray, High Temp Version
- HBL2615F - Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray, High Temp Version



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
 WDK\_CA-HBL2613F-SPEC-EN | REV 1/2024