



# Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2616](#)



Twist-Lock® Industrial Flanged Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal.

## Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Grounding Insulgrip® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #16</li> </ul>

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L5-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK B-29 Catalog Page](#)
- [Catalog Page - WDK N-19 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL2616 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1257\\_INSTALLINST](#)
- [Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK\\_HBL2616\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)

## Related Products

AWG - #8 AWG solid or stranded copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Flanged Receptacle
- Flanged Receptacle

Type

UPC 783585038810

HBL2611BK - Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black

WP2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester

HBL2611 - Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

### Dimensions

Dimensions	2.88 in x 2.88 in x 2.09 in
Display Size	Standard Sized Product
Height	2.09 in
Length	2.88 in
Weight	0.30 lb
Width	2.88 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL2616-SPEC-EN | REV 1/2024